

| Quantity | Reference | Description |
|----------|-----------|---------------------------------------|
| 1 | BR1 | 600V, 1A bridge |
| 1 | C1 | 4.7 μ F/400V electrolytic |
| 1 | C2 | 10 μ F/400V electrolytic |
| 1 | C3 | 47pF 1kV ceramic |
| 1 | C4 | 22 μ F/25V electrolytic |
| 1 | C5 | 4.7nF/250V Y cap |
| 1 | C6 | 0.01 μ F/50V ceramic |
| 1 | C7 | 330 μ F/25V electrolytic |
| 1 | C8 | 100 μ F/25V electrolytic |
| 1 | C9 | 0.01 μ F/50V ceramic |
| 1 | C11 | 0.047 μ F/250V boxcap |
| 1 | D2 | 1N4148 |
| 1 | D3 | STMicroelectronics BYW100-200 |
| 1 | F1 | 0.5A 250V Fuse |
| 2 | J1, J2 | Connectors |
| 1 | L1 | Compostar 2x45mH FUU10S-V24503-Q22650 |
| 1 | L4 | Coilcraft 10 μ H RFB0810-100 |
| 1 | R1 | 12 Ω 5% 1/4W |
| 1 | R2 | 2K Ω 5% 1/2W |
| 1 | R3 | 9.1K Ω 5% 1/4W |
| 1 | R4 | 220 Ω 5% 1/4W |
| 1 | R5 | 1K Ω 5% 1/4W |
| 1 | R6 | 13.3K Ω 1% 1/4W |
| 1 | R7 | 3.48k Ω 1% 1/4W |
| 1 | R8 | 4.7 Ω 5% 1/4W |
| 1 | TR1 | Cramer coil transformer CVP11-021 |
| 1 | U2 | H11A817A or LTV817 optocoupler |
| 1 | U3 | STMicroelectronics TL431 |
| 1 | U4 | STMicroelectronics VIPer12A |
| 1 | W1 | Jumper wire |